


Product comparison : Koru CAM versus Kodak EL

System Features Octagon

Based on Agfa RPS2024 test




Review + implementation


- **Camera / drop-in for :**
 - ◆ processing set-up
 - ◆ exposure set-up
 - ◆ calibration set-up
- Adjustment for :**

Product Colors

CAM



EL



Practical Photographic Properties					
Type	Exp.time(s)(F22)	D.Max.	D.Min	Grad. Toe	Grad
Koru CAM	22	4.20-4.40	0.04	2.5	8
Kodak EL	22	4.20-4.40	0.04	2.5	8

Note: - Koru CAM processed in Koru KF dev. - Kodak EL processed in Kodak RA2000
 - Before switching over to Koru KF developer a cleansing with Koru Chemical Cleaner is obligatory.