


Product comparison : Koru KIR versus Agfa IR

System Features Octagon

Based on Agfa Proset 9800 tests



Review + implementation

● IR 780 nM/ drop-in for :

- ◆ processing set-up
- ◆ calibration set-up
- ◆ exposure set-up

Adjustment for :

Product Colors


KIR



Emulsion side

Back side

IR



Emulsion side

Back side





KIR

Product comparison : Koru KIR versus Agfa IR

Image quality



2400 dpi / 150 lpi

Koru KIR		Agfa IR	
On Agfa Proset 9800 (IR 780nM)			
			
50% = 56%	5% = 6%	50% = 56%	5% = 6%

Practical Photographic Properties

Engine	Agfa Proset 9800			
	KIR	IR		
Property				
Int. Setting	95	95		
Practical density	D.4.10- 4.30	D.4.10- 4.30		
5%	6%	6%		
50%	60%	60%		
95%	99%	99%		

Note: - Koru KIR processed in Koru KF dev. - Agfa IR processed in Agfa G101c developer.
 - Before switching over to Koru KF developer cleansing with Koru Chemical Cleaner is obligatory.